

St. Regis Heat Sealer

Mfg: St. Regis

Model: 90 G

Stock No. SGMT241.16

Serial No. 832094

St. Regis Heat Sealer. Model: 90 G. S/N: 832094. Belt dimensions: 10 ft. L x 12 in. W. Belt height (above floor): 21 in. Maximum aperture: 33 in. H. Minimum aperture: 11-3/4 in. H. Holder bag system: 67 in. L. Hot air heater zone: 30 in. L x 2-1/4 in. H. Sealer zone: 20 in. L x 2-1/4 in. H. Control panel, switch for regulation of temperature from 0°F to 800°F, closer heat on/off, motor start, heater alarm, motor stop. Switch off foot pedal. Electrical requirements: 230 V, 12 amps, 60 Hz, 3 phase. Motor. (4) Casters, 4 in. H for easy positioning. Overall dimensions: 10 ft. 1 in. L x 36 in. W x 53 in. H.



