

Weigh-Tronix Control Scale

Mfg: Weigh-Tronix

Model: WI-125 LED

Stock No. SGMT323.1a

Serial No. 045844

Weigh-Tronix Control Scale. WI-125 LED Indicator. S/N: 045844. Class: III & III HD. Stainless steel weighing platform: 30-1/2 in. L x 24-3/4 in. W. Control with label print-out system. Base on (4) casters. Overall dimensions: 45 in. L x 25 in. W x 60 in. H.





Avery Weigh-Tronix WI-125 LED Indicator

Enclosed in a stainless steel NEMA 4X case, the WI-125 LED Indicator will serve you effectively in wet or dry environments. And its crisp, easy-reading LED display will speed any weighing process.

Features & Benefits

Six function keys - No confusing functions. Train operators in minutes

LED display - Bright, crisp, fast-reading. Speeds weighing process and reduces operator error.

NEMA 4X washdown - Stainless steel enclosure provides corrosion and washdown resistance to rough indoor and outdoor use.

Numeric keypad - Makes tare entry more flexible. Enter known weights from the keypad, or use the TARE key to enter container weights.

RS-232 serial port - Provides link with printers and computers.

Print formatting - Customize your printout with company name, message, character size and location, etc. right from the front panel.

Heavy-duty swivel mounting stand - Adjust the display quickly to the best sight line.

RFI protection - Provides stable weight readings in environments with moderately high levels of RFI radiation.

Options

Time and date