

## Inline Electric Fryer with Fire Control

Mfg:

Model:

Stock No. SGMT517.2a

Serial No.:

Inline Electric Fryer with Fire Control. Inside dimensions: 11 ft. 5 in. L x 13-1/2 in. W x 12 in. H. Maximum tank capacity: 100 gallons. Tank is electrically heated by heater tubes. Chain belt width: 8 in. Fryer features a turn-over mechanism and spraybridge at its mid-section. Turn-over then feeds into outgoing chain conveyor. Height at conveyor outlet: 33 in. Haight Pump, Model: 5D, S/N: 8652781. Leeson Motor, 1/3 hp, 1725/1425 rpm, 115 V, 2.8/3.4-5.6/6.8 FLA, 60/50 Hz, single phase. Dayton Motor, 1/2 hp, 1725 rpm, 115/230 V, 9.6/4.8 FLA, 60 Hz, single phase. Motor drive. Inlets: (1) 7-1/2 in. L x 3-1/2 in. W. Outlets: (1) 10 in. W x 8 in. H (max). Overall dimensions: 12 ft. 3 in. L x 24 in. W x 64 in. H.

