

Waukesha Cherry Burrell Positive Displacement Pump Model 130-U1

Mfg: Waukesha

Model: 130 U1

Stock No. SHCA1914C.

Serial No. 14255 SS

Waukesha Cherry Burrell Positive Displacement Pump. Model: 130-U1. S/N: 14255 SS. Nominal capacity: 140 gpm. Displacement per Revolution: 0.254 gal. Seal Option: single, o-ring. Suitable to 200 psi (13.8 bar) differential pressure. Temperature range -40°F (-40°C) to 300°F (149°C). 0-600 rpm speed range. U.S. Electrical Motor, 5 hp, 1745 rpm, 208-230/460, 15.3-13.6/6.8 amps, 60 Hz, 3 phase. Ultramite Drive, ratio: 6.3, Rpm out: 276 (final). Model 130-U1 pumps are approved for 3A and BISCC applications and feature exclusive, non-galling Waukesha "88" alloy rotors, ease of disassembly for easy cleaning and flexible three-way mounting options. Inlets/outlets: (2) 3 in. dia. NPT fittings. Overall dimensions: 3 ft. 8 in. L x 1 ft. 2 in. W x 1 ft. 6 in. H.



