

2000 Croll Reynolds Stainless Steel Shell & Tube Heat Exchanger – 121 Sq. Ft.

Mfg: Croll Reynolds

Model: ST-10

Stock No: SKFI170.10

Serial No: 79237 / 6751

2000 Croll Reynolds Stainless Steel Shell & Tube Heat Exchanger. Model: ST-10. Serial No: 79237 / 6751. Nat'l Bd. No. 606. Manufactured and certified by Diversified Heat Transfer, Inc. for Croll Reynolds. Material of construction includes all 304 stainless steel except shell and non-product contact surfaces. Heat transfer surface area: 121 square feet. (126) 5/8 in. OD tubes. Shell side: MAWP 150 PSI at 300F, MDMT -20F at 150 PSI. Tube Side: MAWP 150 PSI at 300F, MDMT -20F at 150 PSI. Inlet/outlet sizes: Shell side water: 2 in. Process side: 4 in. vapor inlet and 2 in vapor outlet 1 in. relief valve Overall dimensions: 8 ft. 3 in. L x 1 ft. 3 in. W x 1 ft. 10 in. H.



