

## Stainless Steel Mix Tank – 100 Gallons

**Mfg:**

**Model:**

**Stock No: SIB1194.1**

**Serial No:**

Stainless Steel Mix Tank. Approximate capacity: 100 gallons. (1) Waukesha pump. Size 3. S/N: DO 74129 SS. (2) 3-3/8 in. rotors. Pump has (2) 1-1/2 in. ACME inlet/outlet. Allen Bradley start/stop control box. Doerr Electric Corporation drive: Catalog no. 1750010TQ003Z1. Model: 200375B771. 526 in. lbs., output torque, 10:1 ratio. Alling-Lander Company drive: Model: 3225-FM-L. S/N: 0688/9082. 4.40 max H.P. input, 1800 input rpm, 710 output torque, 5 ratio. Reliance Electric motor: ¾ Hp, 1725 rpm, 230/460 V, 3.44/1.72, 60 Hz, 3 Phase. MagneTek motor: ½ Hp, 1750 Rpm, 90 V, 4.9 A. Tank dimensions: 3 ft. dia. x 1 ft. 11 in. straight wall (117 gallons). 1ft. 1 in. mixing propeller dia. 1-1/4 in. shaft. Inlets/outlets: (2) 1 in. FNPT. (1) 2-1/2 in. ACME. (1) 2 in. FNPT. (1) 1-1/4 in. FNPT. Overall dimensions: 5 ft. 11-1/4 in. L. x 4 ft. 7 in. W. x 5 ft. 10 in. H.











