

1993 G&L Goulds Centrifugal Pump

Mfg: G&L Goulds

Model: SST

Stock No: SMBV003

Serial No:

1993 G&L Goulds Centrifugal Pump. Model: SST. Size: 2x2-1/2-6.304. 304 stainless steel construction. US Motor, 15 hp, 3480 rpm, 230/460 V, 47.0/23.5 amps, 60 Hz, 3 phase. Capacity: 525 gpm @ 70 TDH. Seal option: single mechanical seal. Enclosed impeller and replaceable wear ring for high efficiency and maximum wear life. Standard 150 lb. ANSI raised face flange connections. Inlets: (1) 2-1/2 in. dia. port with a 7 in flange and (4) 1/2 in. bolt holes. Outlets: (1) 2 in. dia. port with a 6 in. flange and (4) 1/2 in. bolt holes. Overall dimensions: 2 ft. 11 in. L x 1 ft. 4 in. W x 1 ft. 6 in. H.



