

## Waukesha Cherry Burrell - Girdler 6 x 48 Votator

Mfg: Chemetron

Model:

Stock No. SNBB103.45

Serial No. A496

Waukesha Cherry-Burrell - Girdler 6 x 48 Votator. S/N: A496. Nat'l Bd: 1133. Stainless steel with 316 stainless steel shaft. Completely refurbished. Inside dimensions: 6 in. dia. x 48 in. L. Eccentric shaft is offset by 1/4 in. Inner shell MAWP: 400 psi @ 400 °F. Jacket MAWP: 150 psi @ 400 °F. Inlet/outlet temperatures: 117/75 °F. Flow rate: 50 gpm (max). Shell thickness: 0.230 in. Jacket thickness: 0.250 in. Scrapers: 6 in. L x 2 in. W; 4-11/16 in. dia. shaft. Baldor Industrial Motor, 20 hp, 1760 rpm, 230/460 V, 50/25 amps, 60 Hz, 3 phase. Foote Bros. Motor Drive. S/N: 2W-85732, 0.59 gear ratio, 38.8 AGMA hp, 1,750 rpm (input), 230 rpm (output). Inlets: (1) 1-1/2 in. dia. media port with 5 in. dia. flange and (4) 5/8 in. dia. attachment holes at a center-to-center distance of 2-3/4 in., (1) 2 in. dia. S-line fitting (product). Outlets: (1) 1-1/2 in. dia. media port with a 5 in. dia. flange and (4) 5/8 in. dia. attachment holes at a center-to-center distance of 2-3/4 in., (1) 2 in. dia. S-line fitting (product). Overall dimensions: 120 in. L x 20-1/2 in. W x 54 in. H.





