

## Flex Top Chain Dual Conveyor

Mfg:

Model:

Stock No. SNPM030.a

Serial No.:

Flex Top Chain Dual Conveyor. (2) SM Cyclo motors, 1/2 hp, 1740 rpm, 230/460 V, 2.1/1.1 amps, 60 Hz, 3 phase. (2) SM Cyclo motor drives, 1/2 hp, output rpm: 83.3, ratio: 21. Conveyor dimensions: 9 ft. 5 in. L x 7-1/2 in. W. From belt to floor: 16 in. H. Clearance dimensions: maximum 10-1/2 in. W, minimum 4 in. W. Missing support (legs). Overall dimensions: 10 ft. 9 in. L x 50 in. W x 24 in. H.

