

Stephan Microcut Emulsifier

Mfg: Stephan

Model: MCH-D100-11/C

Stock No: SNPM045.11a

Serial No: KZ14.932

Stephan Microcut Emulsifier. Model: MCH-D100-11/C. S/N: KZ14.932. Capacity: 17,600 lbs/hr (8000 kg/hr). The Stephan Microcut is a multifunctional fine cutting and dispersing system. Horizontal construction with double stage rotor-stator assembly. Benefits of the Microcut: efficient fine grinding, ideal cutting, homogenous mixing, optimal powder dispersing, stable emulsions, constant product quality, and ease of operation. Cutting disc diameter: 7-1/2 in. Stephan Motor, 165 hp(125 kW), 3565 rpm, 440 V, 195 amps, 60 Hz, 3 phase. Inlets: (1) 3 in. dia. S-line fitting. Outlets: (1) 3 in. dia. I-line fitting. Overall dimensions: 6 ft. 2 in. L x 2 ft.9 in. W x 4ft. 4 in. H.







