

## Super Trol Temperature Control System- 1 HP

Mfg: Super Trol

Model: MCI-975-U

Stock No. SNSL042.a

Serial No. SS-81-351-1

Super Trol Temperature Control System- 1 HP. Model: MCI-975-U. S/N: SS-81-351-1. Maximum fluid temperature: 200 °F. Maximum fluid pressure: 60 PSIG. Fluid: Water. Power: 16 FLA. BTUH: 9 kW. Return- 60 PSI. Discharge- 100 PSI. Centrifugal Pump with Baldor Motor, 3 hp. 3450 rpm. 203-208/460 V, 7.8-7.4/3.7 amps, 60 Hz, 3 phase. Athena temperature controller. Federal Vibratone Sound Horn, Model: 350, Series B-1, electrical requirements: 120 V, 18 Amps. 60 Hz. Warren Electric Corp. Heater, Model: XBF9-460-1259, 900 Watts, 460 VAC. Maximum pressure: 300 psig. Taco pressure relief valve, Model 334-1. Inlets: (2) 1/2 in. dia. Outlets: (3) 1/2 in. dia. Overall dimensions: 54-3/4 in. L x 27 in. W x 60 in. H.



