

## Stephan Microcut Emulsifier

Mfg: Stephan

Model: MCHD100-11CS

Stock No. SNPM046.11a

Serial No. 712.449.02

Stephan Microcut Emulsifier. Model: MCHD100-11CS. S/N: 712.449.02. Capacity: 17,600 lbs/hr (8000 kg/hr). The Stephan Microcut is a multifunctional fine cutting and dispersing system. Horizontal construction with double stage rotor-stator assembly. Benefits of the Microcut: efficient fine grinding, ideal cutting, homogenous mixing, optimal powder dispersing, stable emulsions, constant product quality, and ease of operation. Cutting disc diameter: 7-1/2 in. Stephan Motor, 200 hp (150 kW), 2970 rpm, 440 V, 225 amps, 60 Hz, 3 phase. Inlets: (1) 3 in. dia. S-line fitting. Outlets: (1) 3 in. dia. I-line fitting. Overall dimensions: 74 in. L x 33 in. W x 52 in. H.







