

Hot Water Set with Shell and Tube Heat Exchanger

Mfg:

Model:

Stock No. SPGP030.3

Serial No.

Shell and tube hot water set with Armstrong shell and tube heat exchanger surge tank.

- Pump trap.
- Tank: National board number 77591. MAWP 125 psi at 240 °F. MAWP 861 KPA at 115 °C. MDMT 18 °F at 125 PSI. Size 60.
- Year built 1999.
- Armstrong heat exchanger certified by S.A. Armstrong limited.
- Tube Side: 150 psi, 375 F, 150 psi.
- Shell Side: 150 psi, 375 F, 35 F, 150 psi.
- S/N 101204, Model S-64-2-2.
- Year Built 1998.
- Surge Tank: Max Pressure 160 psi, Max temp: 350 °F.
- Armstrong Pump:
 - Model 2X1X10 4280.
 - Pump Capacity: 35, US GPM 80 ft.
 - Motor 3 hp, 1,800 rpm, Tag: IMP DIA 8.897.
 - Pressure gauge 100 psi.



