

Mettler Toledo Hi-Speed Checkweigher

Mfg: Mettler Toledo

Model: CM6300WD CM

Stock No. SPPF258.

Serial No. 13704

Mettler Toledo Hi-Speed Checkweigher. Control panel, Model: CM, S/N: CM-1041. Dwg: D2-81-147. Maximum capacity: 50 lbs. Conveyor speed: 75 ft/min; 15 pkg/min. Features touchpad controls and light signal indicators. Electrical requirements: 115V, 1.0 FLA, 60 cycles, 1 phase. Overall dimensions for control panel: 24 in. L x 15 in. W x 64 in. H. Hi-Speed Checkweigher, Model: CM6300WD CM. S/N: 13704. Conveyor. Model: CM60CM-MS, S/N: 9849, Job No: 91020071. Maximum belt width: 8 in. Height at conveyor inlet/outlet: 37-1/2 in. H. Conveyor also features a Banner Multi-Beam laser scanner and Allen-Bradley power switch. Reliance Motor, 1/2 hp, 1725 rpm, 208-230/460 V, 2.2-2.2/1.1 amps, 60 Hz, 3 phase. Boston Motor Drive. Overall dimensions for entire unit (including control panel): 40 in. L x 36 in. W x 64 in. H.



