

Krispykist Screw Blender-100 Gallon

Mfg: Krispykist

Model:

Stock No. SPPP1019.1a

Serial No.:

Krispykist Screw Blender-100 Gallon. Screw auger dimensions: 12 in. diameter x 18 in. H. Piston maximum stroke (screw auger): 80 in. H. Tank rotates for additional blending. Auger on/off switch, tank on/off switch. Oberdorfer hydraulic pump. Baldor Industrial Motor (screw auger): 1/3 hp, 1725 rpm, 208-230/460 V, 1.8-1.6/0.8 amps, 60 Hz, 3 phase. Morse Motor Drive, ratio: 7.5, final rpm: 230. Baldor Industrial Motor (rotating base): 3/4 hp, 1725 rpm, 208-230/460 V, 3.2-3/1.5 amps, 60 Hz, 3 phase. Overall dimensions: 46 in. L x 36 in. W x 58 in. H.

