

E.L. Nickell Horizontal Ammonia Receiver – 885 Gallons

Mfg: E.L. Nickell

Model:

Stock No: SSFF0109.2

Serial No: 32616

E.L. Nickell Horizontal Ammonia Receiver. Serial no: 32616, Natl. Bd. no: 30611. Approximate capacity: 885 gallons. Receiver dimensions: 48 in. diameter x 113 in. straight wall. Maximum pressure: 150 psi. Maximum design temperature: 650 °F. Minimum design temperature: -20 °F. Mounted on steel platform.

Overall dimensions: 14 ft. L x 6 ft. W x 7 ft. 9 in. H.



