

Moyno 6M4 Progressing Cavity Pump

Mfg: Moyno

Model: 6M4

Stock No. SPPP770.2

Serial No. AS53027

Moyno 6M4 Progressing Cavity Pump. Model: 6M4. S/N: AS53027. Stainless steel pump body. Maximum rpm: 1050. Capacity: 8.5 gpm at 87 psi. Final rpm: 434. Motor (enclosed): 10 hp, 1735 rpm, 230/460 V, 27/13.5 amps, 3 phase. Pulley ratio: 4 to 1. The Moyno progressive cavity pump is a single screw rotary pump. The pumping action is created by the single helical rotor rolling eccentrically in the double threaded helix of the stator (nitrile). Typical applications include high-pressure water, pastes & gels, food, wastes & by-products, chemical feed & sampling, and coolants & lubricants. Inlets: (1) 3 in. diameter, flange: 7 1/2 in. diameter with (4) thru-holes at a center-to-center distance of 6 in. Outlets: (1) 2 in. NPT (male). Overall dimensions: 6 ft. L x 3 ft. in. W x 2 ft. 3 in. H.

