

FES / Dunham - Bush Screw Compressor Package – 400 HP

Mfg: FES

Model: 350 / 2510

Stock No: SSFF0186.120

Serial No:

FES / Dunham - Bush Screw Compressor Package. Model: 350 / 2510. Capacity rating: 316 tons at 414 bhp with a 10°F suction temperature, 95°F condensing temperature, and 10°F liquid subcooling. Displacement: 1061 cfm. FES Micro II E controls. Toshiba World Energy Series, 3-phase induction motor: Model: B4002VLG3B3, Serial no. 10045606, 400 hp, 3540 rpm, 460V, 470 amps: service factor: 1.15, 60 Hz, 3 phase. Design: B, continuous duty, drip proof enclosure type: TTK. Henry Valve Co. ammonia valve, cat. no. 5602, size ¾ in., Prince Valve Inc. P/N 33574, size: 4. Hours on compressor: 33774. Overall dimensions: 13 ft. L x 4 ft. 3 in. W x 7 ft. 11 in. H.





