

Stainless Steel Vibratory Shaker

Mfg:

Model:

Stock No. SSLP108.3

Serial No.:

Stainless Steel Vibratory Shaker. High Efficiency motor, 1-1/2 hp, 1730 rpm, 230/460 V, 4.8/2.4 amps, 60 Hz, 3 phase. Vibrating Shaker system, No: 86480, size: 10CF. Stainless steel bed: 82 in. L x 36 in. W x 6 in. H. Opening: 27 in. L. Product outlet height: 23 in. (12) Vibrating feeder springs: 2 in. W x 18 in. H. Overall dimensions: 95 in. L x 46-1/2 in. W x 56 in. H.

