

Stainless Steel Dewatering Shaker

Mfg:

Model:

Stock No. SSLP117.2

Serial No.:

Stainless Steel Dewatering Shaker. High efficiency motor, 1.5 hp, 1725 rpm, 230/460 V, 4.8-2.4 amps, 60 Hz, 3 phase. Shaker system. Platform: 43 in. L x 59 in. L x 4 in. H. Platform screen: 41-1/2 in. L x 35-1/2 in. W. (16) Vibrating feeder springs: 18 in. L x 2 in. W. Product exit: 15 in. H. Overall dimensions: 77 in. L x 60 in. W x 33 in. H.



