

Timing Conveyor

Mfg:

Model:

Stock No. SUBF247.1a

Serial No.

Timing Conveyor.

- Conveyor is disassembled in 2 parts.
- Electric Box:
- Underwriters laboratories (Hoffman), Cat No. A-8064CHNFSS. Enclosure Type: 4.4X.12.
- D.C Motor Speed Control: (2), KB Electronics. Model KBPC-240 D. Input: 120/240 V, 15 amps, 50/60 Hz. Output: 10.2 amps (DC). DC Gear Motor: (2), Dayton. HP/CV: 1/20. 90 V, 0.6 amps, 109 rpm, 27 (lb-in) Torque. Ratio 16.5. Legs: 3 at 22 in. H. (1st part). 2 at 18-½ in. (2nd part).
- Overall dimensions: (1st Part): 33-½ in. L x 26 in. W x 41 in. H.
- Overall dimensions for 2nd part: 9-½ in. W x 35-½ in. L x 29 in. H.

