

Hercules Barrel Dumper

Mfg: Hercules

Model: HI-110SP-C3396

Stock No. SSPN206.1

Serial No. D5529

Hercules Barrel Dumper. Model: HI-110SP-C3396. S/N: D5529. Capacity: 750 pounds. Lesson motor: $\frac{3}{4}$ hp, 1725 rpm, 115 & 208-230 V, 10.8 & 5.4 FLA, 60 Hz. Container: 22-3/4 in. dia. x 60 in. H. Dumper mechanism: 45 in. H. (4) Casters. Switch on/off. Discharge height is 37 in. when fully tilted. Maximum height of 91 in. Overall dimensions: 53 in. L x 36 in. W x 61 in. H.

