

Un-used Trane Air Handling Unit

Mfg: Trane

Model:

LPCAA17F1E02K000000300FCAA000A0E00000

Stock No. SYCM001.7

Serial No. 705021715

Un-used Trane Air Handling Unit. Model: LPCAA17F1E02K000000300FCAA000A0E00000. S/N: 705021715. S.O: L3S143AB. Horizontal front/top air throw. 17 sq. ft. of coil. Nominal airflow: 8,500 cfm. Insulation thickness: 1 in. Blower Motor, 3 hp, 4.0 FLA. Maximum inlet water temperature 200 °F (93 °C). Maximum water pressure 300 psig (14 bar). System requirements: 460 V, 60 Hz, 3 phase. Maximum ampacity: 6.0 amps. Maximum current protection: 15.0 amps, Drive input current: 4.8 amps. Trane Packaged Climate Changer air handlers are one of the most cost-effective packaged units designed to meet industry standards for indoor air quality on the market today. Widely used in office buildings, hospitals, schools, and other traditional air-handling applications, these units are UL-listed and ARI-rated and can be used in constant-volume or variable-volume systems. Inlets: (1) 2-1/2 in. dia. NPT (male, water in), (1) in. W x in. H. Outlets: (1) 2-1/2 in. dia. NPT (male, water in), (1) 24 in. L x 20 in. H discharge (air throw). Overall dimensions: 91 in. L x 62 in. W x 52 in. H.





