

Aquafine Corporation CSL™ Series UV Sterilizer

Mfg: Aquafine Corporation

Model: CSL-12R

Stock No: TACJ0455.4

Serial No: I112011

Aquafine Corporation CSL™ Series UV Sterilizer. Model: CSL-12R. S/N: I112011. Disinfection flow rates: 156 gpm @ 99% UVT. Materials of construction: 316L stainless steel treatment chamber and a 304 stainless steel control panel. Paragon Electric Co. Timing Motor: Model no. 7007-00. 120 V, 60 Hz. Minimum and maximum operating temperature ranges: 50°F → 100°F. Maximum operating pressure: 120 PSI. Required operating power: 540 watts. Power requirements: 118 VAC, 7.5 A, 60 Hz. Inlets/outlets: (2) 3-1/2 in. flange with (4) 3/4 in. mounting holes dia, 4-1/4 in. adjacent, 6 in. opposite, (1) 3/4 in. FNPT drain. U.V. lamp operational display Applications include: Disinfection and ozone destruction with markets to include: Food & Beverage, Life Sciences, and Microelectronics. Sterilizer dimensions: 3 ft. 8 in. L X 1 ft. 2 1/2 in. W X 1 ft. 11 in. H. Overall dimensions: 3 ft. 8 in. L X 1 ft. 6-3/8 in. W X 4 ft. 2-3/4 in. H.









