

Fristam Liquid-Ring Pump

Mfg: Fristam

Model: FZX100

Stock No: TACJ0230.6

Serial No: FZX100973690

Fristam Liquid Ring Pump. Model: FZX100. S/N: FZX100973690. Flow rate for new pump is approximately 80 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Impeller dia: 6-3/4 in. Baldor Electric motor: 3 Hp, 1725 Rpm, 208-230/460 V, 8.5-8.2/4.1 A, 60 Hz, 3 Phase. Ideal for handling products with entrained air. Maintains prime with its specially designed impeller and housing. Its vacuum capability makes it an excellent CIP return pump when complete removal of fluids is necessary. (1) 2 in. s-line inlet. (1) 2 in. s-line outlet. Overall dimensions: 1 ft. 11-1/4 in. L x 9-3/4 in. W x 9-5/8 in. H.





