

Rigidbilt Inc. Evaporator – 9.5 Tons

Mfg: Rigidbilt

Model: AF160-63RAHG

Stock No: TACJ1161F

Serial No: 37300

Rigidbilt Inc. Evaporator. Model: AF160-63RAHG. Serial No: 37300. Rated capacity: 9.5 tons using recirculated R-717, 16,000 cfm. Coil: 6 rows of $\frac{3}{4}$ in. dia. tubes with (3) fins per inch. (2) 30 inch diameter axial fans. This unit features hot gas defrost. (2) Toshiba 3 hp 3 phase 230/460 V 8.5/4.3 A 1735 rpm. Inlets/outlets: (1) 2-1/2 in. NPT, (1) 2 in. drain, (1) 1 in. NPT. Inlets/outlets: (1) 1 in. NPT and (1) 2 in. NPT. Listed shipping weight: 1930 lbs. Overall dimensions: 10 ft. 2 in. L x 3 ft. 11 in. W x 3 ft. 9 in. H.



