

Reco / Frick RWB-100 Package less Compressor

Mfg: Reco / Frick

Model: RWB-100

Stock No.: TFAR066.37

Serial No.: GDSH193S0055P

Reco / Frick RWB-100 Package less compressor. The bare compressor has been removed and sold; however the remainder of the package is still available. Previous compressor specs: Frick Rotary Screw Compressor model: GDSH193S0055P, NH3 / R22, 4500 max RPM, Vi: 2.5-5.0, 362 max PSI. Previously used with ammonia refrigerant. Parts still present include the oil separator, oil cooler, oil pump, micro panel, suction strainer, etc. RECO 24" Oil Separator 250 PSIG at 300F, MDMT: -20F at 350 PSIG. Test: 375 PSIG. RECO Oil Cooler: S/N: M903210 G, shell MAWP: 350 PSI at -20F/300F, tubes 250 PSI at -20F/300F, Blackmer Oil Pump. Toshiba High Efficiency Motor: 100 HP, 230/460V, 23/115 amps, 3530 RPM, 60 Hz, 3-phase. Frick microprocessor controller. *PDF Manual Available. Overall dimensions: 141 in. L x 58 in. W x 93 in. H.





