

S. A. Armstrong Shell & Tube Heat Exchanger

Mfg: S.A. Armstrong LTD.

Model:

Stock No: TMCB279A

Serial No: 68030

S. A. Armstrong Shell & Tube Heat Exchanger. S/N: 68030. Cat no. WS 65-2E1. Date of MFR. Nov/83. Max operating temp: 375 °F. Max. Working Press. Shell: 150 PSI. Max. Working Press. Tubes: 150 PSI. 2 pass heat exchanger. (13) Inner tube dimensions: 5 ft. L x 5/8 in. dia. Inlets/outlets: (2) 2-1/4 in. FNPT. (1) 3/4 in. FNPT. (1) 1-1/4 in. FNPT. (1) 1-1/2 in. FNPT. Overall dimensions: 6 ft. 1-1/2 in. L x 10-1/2 in. W x 11 in. H.



