

Trane CenTraVac Hermetic Centrifugal Compressor- 260 Ton

Mfg: Trane

Model: CVHE-025B-AK-
2GB23511DE1A11DEZA000

Stock No. THHS001.5

Serial No. L86E38330

Trane CenTraVac Hermetic Centrifugal Compressor- 260 Ton. Model: CVHE-025B-AK-2GB23511DE1A11DEZA000. S/N: L86E38330. Refrigerant: R-11. System requirements: 208 V, 60 Hz, 3 phase. Maximum refrigerant working pressure (hi/lo): 15/1.5 psig. Factory test pressure (hi/lo): 45/4.5 psig. Field leak test pressure: 8 psig max. Inlets: (1) 18 in. dia. suction port. Outlets: (1) 10 in. dia. discharge port. Overall dimensions: in. L x in. W x in. H.

