

Square D Transformer

Mfg: Square D

Model:

Stock No: TMCB547

Serial No:

Square D Transformer. Cat no. C9T2F. KVA: 9. WGHT: 265. H.V. 480, L.V. 208/120. H.V. Amps. 10.8, L.V. Amps. 24.9. 60 Hz. Date code: 9602. Rain proof enclosure: Type 3R. Overall dimensions: 1 ft. 7 in. L x 1 ft. 3 in. W x 11-3/4 in. H.





SQUARE D COMPANY 65 MADE IN USA

SORGEL TYPE ST INSULATED TRANSFORMER

CAT. NO: C9T2F KVA: 9 WGT: 265

H.V.: 480 DELTA H.V. AMPS: 10.8 x 12

L.V.: 208Y/120 L.V. AMPS: 24.9 HZ: 60

180 DEG C INS SYSTEM, 115 DEG C RISE, 65TS188

RAINPROOF ENCLOSURE: TYPE 3R DATE CODE: 9602

READ INSTRUCTION MANUAL: 7410/20-S

STYLE NO: C9T2F

SERIAL NO:

TAP CONNECTIONS

VOLTAGE	TAP
480	H1-H2-H3
420	H1-H2-H3
432	H1-H2-H3

703 6315909-00

DANGER
TO AVOID ELECTRICAL SHOCK DO NOT REMOVE COVER WHILE TRANSFORMER IS ENERGIZED

FOR FIELD CONNECTIONS

USE WIRE INSULATED FOR A MINIMUM OF 90° C AND SIZE ON THE BASIS OF 60° C AMPACITY

UL SF 65TS188

W4 H1 H7 H2 H3 H4 H5 H6 H7 H8 H9 H10 H11 H12 H13 H14 H15 H16 H17 H18 H19 H20 H21 H22 H23 H24 H25 H26 H27 H28 H29 H30 H31 H32 H33 H34 H35 H36 H37 H38 H39 H40 H41 H42 H43 H44 H45 H46 H47 H48 H49 H50 H51 H52 H53 H54 H55 H56 H57 H58 H59 H60 H61 H62 H63 H64 H65 H66 H67 H68 H69 H70 H71 H72 H73 H74 H75 H76 H77 H78 H79 H80 H81 H82 H83 H84 H85 H86 H87 H88 H89 H90 H91 H92 H93 H94 H95 H96 H97 H98 H99 H100

SQUARE D COMPANY

QUIET QUALITY

SORGEL TYPE ST INSULATED TRANSFORMER

CAT. NO: C9T2F KVA: 9 WGT: 265

H.V.: 480 DELTA H.V. AMPS: 10.8 x 12

L.V.: 208Y/120 L.V. AMPS: 24.9 HZ: 60

180 DEG C INS SYSTEM, 115 DEG C RISE, 65TS188

RAINPROOF ENCLOSURE: TYPE 3R DATE CODE: 9602

READ INSTRUCTION MANUAL: 7410/20-S

STYLE NO: C9T2F

SERIAL NO:

TAP CONNECTIONS

VOLTAGE	TAP
480	H1-H2-H3

703

W4 H1 H7 H2 H3 H4 H5 H6 H7 H8 H9 H10 H11 H12 H13 H14 H15 H16 H17 H18 H19 H20 H21 H22 H23 H24 H25 H26 H27 H28 H29 H30 H31 H32 H33 H34 H35 H36 H37 H38 H39 H40 H41 H42 H43 H44 H45 H46 H47 H48 H49 H50 H51 H52 H53 H54 H55 H56 H57 H58 H59 H60 H61 H62 H63 H64 H65 H66 H67 H68 H69 H70 H71 H72 H73 H74 H75 H76 H77 H78 H79 H80 H81 H82 H83 H84 H85 H86 H87 H88 H89 H90 H91 H92 H93 H94 H95 H96 H97 H98 H99 H100