

Jackson Conserver XL Door Style Dishwasher

Mfg: Jackson

Model: Conserver XL

Stock No. VCMT001.2

Serial No. OLK9515M

Jackson Conserver XL Door Style Dishwasher. Model: Conserver XL. S/N: OLK9515M. Capacity: 37 racks per hour, 925 dishes and glasses per hour. Pump capacity is 55 gpm. Operating cycle: wash time is 42 seconds, rinse time is 25 seconds, dwell time is 23 seconds. Minimum water volume is 1.49 gallons. Wall clearance (minimum) 4 in. Inside clearance (height): 17-1/4 in. (7) Sprayers mounted on 24 in. L tubes. Ace Pump Corp. Centrifugal Pump, S/N: 43256. Century AC Motor, 3/4 hp, 3450 rpm, 115/230 V, 11.4/5.7 amps, 60 Hz, 3 phase. Inlets: 3/4 in. dia. ACME male fitting. Outlets: (1) 1/4 in dia. water, (1) 1/8 in. dia. soap, (1) 2 in. dia. water chute. Overall dimensions: 33 in. L x 30 in. W x 68-3/4 in. H.



