

Breddo LOR Heavy-Duty High Speed Likwifier- 300 Gallon

Mfg: Breddo Likwifier

Model: LORW

Stock No. 250.cCCFF02.90

Serial No. D19571-3

Breddo LOR Heavy-Duty High Speed Likwifier- 300 Gallon. Model: LORW. S/N: D19571-3. Heating medium: steam/water. Shell material: 12 gauge, type 304 stainless to a No. 4 polished finish. Heat transfer surface: type 304 stainless steel Temp-Plate heat transfer surface designed for 90 psi @ 350 °F. Dimpled cone bottom tank with side-scrape agitation. (56) 4 in. L x 1 in. W side-surface scrapers. Man way diameter: 16 in. Breddo Motor, 50 hp, 1770 rpm, 1819 rpm (final), 208-230/460 V, 128-116/53 amps, 60 Hz, 3 phase. Sew-Eurodrive Motor, 5 hp, 1680 rpm, 230/460 V, 13.6/6.8 amps, 60 Hz, 3 phase. Sew-Eurodrive Speed Reducer, 125 ratio, 13 rpm (final). For a quarter of a century the Breddo Likwifier blender is the preferred choice for highly viscous products from cheese slurries to whey concentrates from tomato paste to gum concentrates, the Likwifier delivers homogeneity in less than 5 minutes. Inlets: (1) 3/4 in. dial. FNPT, (1) 1 in. dial. MPT (jacket), (1) 1-1/2 in. dial. MPT (jacket), (2) 2 in. dial. S-line fittings. Outlets: (1) 1 in. dia. MPT (jacket), (1) 1-1/2 in. dia. MPT (jacket), (1) 2-1/2 in. dia. S-line fitting. Overall dimensions: 81 in. L x 62 in. W x 100 in. H.









