

**FES 505XB / Howden 255-1.45 M Booster Rotary Screw Compressor Package – 200 HP**

**Mfg: FES Howden**

**Model: 505XB / 255-1.45 M**

**Stock No: HDCF246**

**Serial No: MK4-008**

FES 505XB / Howden 255-1.45 M Booster Rotary Screw Compressor Package- 200 HP. Model: 505XB. S/N: MK4-008. Refrigerant: ammonia. MDWP: 350 PSIG. Hydrostatic test pressure: 525 PSIG. Vi ratio: 3.6. FES oil separator, S/N: 87045, Nat'l Bd No: 2914. MAWP: 250 PSI. MDMT: 200°F. Toshiba electric motor. 200 hp, 3540 rpm, 230/460 V, 470/235 amps, 60 Hz, 3 phase. Viking rotary hydraulic oil pump, Model: AV428AL, S/N: 10874147. Magnetek Century electric motor, 7-1/2 hp, 1170 rpm, 208-230/460 V, 21-19.2/9.6 amps, 60 Hz, 3 phase. FES Micro II control panel, Model: FES505XB, S/N: 8700230301, power supply: 120 V, 2.5 amps, 60 Hz, 3 phase. Outlets: (1) 2 in. dia. pressure relief valve, (1) 5 in. dia. refrigerant discharge port. Overall dimensions: 14 ft. 4 in. L x 4 ft. 7 in. W x 8 ft. H. Compressor runtime: 90,383 hrs.







