

2000 Wescold Inc. Shell and Tube Heat Exchanger - 294 Sq. Ft.

Mfg: Wescold Inc.

Model:

Stock No: CNPR006

Serial No: 4217

2000 Wescold Inc. Shell and Tube Heat Exchanger. S/N: 4217. Nat'l Bd No. 3855. Tube material: carbon steel. Number of passes: 7. Number of tubes: 71. Tube dimensions: 1-1/2 in. dia. x 10 ft. 6-1/2 in. L. Heat transfer surface area: approx. 294 sq. ft. Approximate tube volume: 68 gallons. Shell side MAWP: 300 psi @ 650°F. Shell side MDMT: -20°F @ 300 psi. Inlets: (1) 3-1/2 in. dia. flanged port, (1) 3 in. dia. port, (1) 1 in. dia. port. Outlets: (1) 3-1/2 in. dia. flanged port, (1) 1 in. dia. port, (1) 2 in. dia. port. Overall dimensions: 12 ft. 1 in. L x 1 ft. 11 in. W x 2 ft. 7 in. H.









NAT'L BD. NO. 3855
CERTIFIED BY
WESCOLD INC. SEATTLE, WA.
SHELL SIDE TUBE SIDE
MAWP. 300 PSI AT 650°F PSILAT °F
MDMT. 20°F AT 300 PSI °F AT PSI
ES SERIAL NO. 4217
YEAR BUILT 2000

NAT'L BD. NO. 3855
CERTIFIED BY
WESCOLD INC. SEATTLE, WA.
SHELL SIDE TUBE SIDE
MAWP. 300 PSI AT 650°F PSILAT °F
MDMT. 20°F AT 300 PSI °F AT PSI
ES SERIAL NO. 4217
YEAR BUILT 2000

NAT'L BD. NO. 3855
CERTIFIED BY
WESCOLD INC. SEATTLE, WA.
SHELL SIDE TUBE SIDE
MAWP. 300 PSI AT 650°F PSILAT °F
MDMT. 20°F AT 300 PSI °F AT PSI
ES SERIAL NO. 4217
YEAR BUILT 2000