

Stainless Steel Sifter Shaker

Mfg: Not Specified

Model:

Stock No.: CFPH208

Serial No.:

Stainless Steel Sifter Shaker. Infeed hopper dimensions: 3 ft. 2-1/2 in. L x 1 ft. 3 in. W x 8-1/2 in. H. Vibco Electronic Vibrator, Model: 2P-150-03, S/N: 32627, continuous duty power supply: 3450 rpm, 230/460 V, 0.6/0.3 amps, 60 Hz, 3 phase. Cougar Industries Pneumatic Vibrator, Model: ABF-35, minimum starting pressure: 5 psi, torque: 0.210 in.-lbs, weight: 5-7/8 lbs, performance @ 20 psi: 7,000 rpm, 292 force, 7.1 cfm, performance @ 40 psi: 8,200 rpm, 401 force, 10.9 cfm, performance @ 60 psi: 10,750 rpm, 689 force, 14.7 cfm, performance @ 80 psi: 11,500 rpm, 789 force, 18.9 cfm. Drive with 6-1/2 in. dia. pulley. Inlets: (1) 3 ft. 2-1/2 in. L x 1 ft. 3 in. W x 8-1/2 in. H. Outlets: (1) 4 in. dia. discharge, (1) 6 in. dia. discharge. Overall dimensions: 5 ft. 4 in. L x 3 ft. 8 in. W x 3 ft. 2 in. H.









