

Goring Kerr Metal Detector with Pneumatic Reject Mechanism

Mfg: Goring Kerr

Model: TEK21 DSP

Stock No. sEELD253.1

Serial No. 46131-5

Goring Kerr Metal Detector with Pneumatic Reject Mechanism. Model: TEK21 DSP. S/N:46131-5. Detector power supply: 110 V, 50/60 Hz, single phase. Conveyor belt dimensions: 3 ft. 11 in. L x 9-1/2 in. W. Maximum aperture/clearance: 14 in. W. x 4 in. H. Pneumatic reject mechanism dimensions: 9 in. L. x 2 in. W. Century Electric Motor, 1/4 hp, 1725 rpm, 115/230 V, 4/2 amps, 60 Hz, single phase. Conveyor Infeed height: 2 ft. 4 in. Exit height: 2 ft. 6 in. H. Overall dimensions: 4 ft. L x 2 ft. 9 in. W x 3 ft. 3 in. H.





