

## Frick Horizontal Ammonia Receiver-150 Gallon

Mfg: Frick

Model:

Stock No.: tFEC09

Serial No.:

Frick Horizontal Ammonia Receiver-150 Gallon. Nat'l Bd: 33313. Inside straight-wall dimensions: 3 ft. dia. x 3 ft. L. MAWP: 250 psig & F.V. Maximum design temperature: -20 to 650°F. Minimum design temperature: -50°F. Max pressure @ minimum temperature: UCS-66100 psig. Mat'l SA: 285-C-FLG-T.S. 55000. Shell thickness: 0.5 in. Head thickness: 0.406 in. Radius: 2:1. Refrigerant Specialties Refrigerant Solenoid Valve. S/N: A11205. Design pressure: 300 psig. (2) Parker Fluid Float Switches, 120 VAC, 240 VAC, 7 amps. Inlets: (1) 2 in. dia. flanged port, (1) 1-1/2 in. dia. port. Outlets: (1) 3/4 in. dia. NPT drain port, (2) 1 in. dia. ACME fittings, (1) 1 in. dia. port, (2) 2 in. dia. flanged ports. Overall dimensions: 7 ft. 4 in. L x 7 ft. W x 7 ft. 4 in. H.





