

Brown International Corp. Model 202 Paddle Pulper / Finisher

Mfg: Brown International Corp.

Model: 202


Stock No: tRLAQ01


Serial No: 203-67


Brown International Corp. Paddle Pulper / Finisher. Model: 202. S/N: 203-67. Motor specifications: 10 Hp, 1200 rpm, 230/460 V, 27/13.5 A, 60 Hz, 3 phase. Pulley's dia. 7-3/4 in. driver, 1 ft. 3/4 in. driven. 5/8 in. screen holder hole dia. Overall paddle shaft dimensions: 4 ft. 1 in. L x 1 ft. W (Paddle is adjustable). Paddle dimensions: 3 ft. 6-1/2 in. L x 3 in. paddle width. Paddle weight: 13 lbs. 6 oz. Inside processing area: 3 ft. 3-1/2 in. L x 1 ft. 9 in. W. Inlets/outlets: (1) 8 in. x 4 in. rectangular flange with (10) 1/4 in. mounting holes. (1) 6 in. x 4 in. port. (1) 4 in. port. (1) 2 in. S-line. Applications include the reductions of apricots, tomatoes, pumpkins, pears, apples, plums, berries, prunes and figs to pulp free of seeds, skins and fibers. Products such as citrus juices, jam, soup, peanut butter, jelly and fruit nectar can be finished to uniform consistency. Overall dimensions: 5 ft. 9-1/2 in. L x 2 ft. 9 in. W x 3 ft. 9 in. H.











MANUFACTURED BY
 BROWN INTERNATIONAL CORP.
 COVINA, CALIFORNIA
 MODEL NO. 202
 SERIAL NO. 203-67



10 0B7058-3
 1200
 284U ABFF
 CD 5480 EPOXY TREATMENT 40
 230/460
 3 60 27/13/5



¹
 30873-2 R.H.
 NEW WT. 13 LBS 6 OZ