

Waukesha 200 Positive Displacement Pump

Mfg: Waukesha

Model: 200

Stock No: 72.1R-498A.16

Serial No: SEP707SS

Waukesha Positive Displacement Pump. Model: 200. S/N: SEP707SS. Flow rate for new pump is 300 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Maximum allowable speed: 600 rpm. Single, mechanical seal option. Rotors, body, and product contact parts are constructed of stainless steel. Waukesha 200 pumps run with close tolerances which result in low slip, high volumetric and mechanical efficiencies resulting in longer-than-normal wear. Pump is equipped with twin-lobe rotors which are suitable for most applications in the following industries: milk products, vegetables, fruits, flavorings, bakeries, and meats. Inlet/outlet: (2) 8-1/8 in. rotors. (2) 4 in. S-line. Overall dimensions: 1 ft. 10-5/8 in. L x 1 ft. 3 in. W x 1 ft. 6 in. H.





