

APV Dual Tube Cooker

Mfg: APV

Model:

Stock No. tSPPM01.

Serial No.

APV Dual Tube Cooker. Upper/lower tube dimensions: 7-1/2 in. dia. x 84 in. L. Auger screw diameter: 7 in. Upper tube motor and gear drive: Baldor Industrial Motor, 1 hp, 1725 rpm, 208-230/460 V, 3.5-3.2/1.6 amps, 60 Hz, 3 phase. Sterling Electric Speed-Trol Variable Speed Drive, 4200 rpm (max), 700 rpm (min). Lower tube motor and gear drive: Baldor Super-E Motor, 1-1/2 hp, 1740 rpm, 230/460 V, 4/2 amps, 60 Hz, 3 phase. Nord Motor Drive, 112.23 ratio, 16 rpm (final). Inlets: (1) 15-3/4 in. L x 15 in. W infeed hopper, (1) 4 in. dia. Q-line fitting. Outlets: (1) 3 in. dia. Q-line fitting. Overall dimensions: 12 ft. L x 55 in. W x 64 in. H.

Product motor and gear drive: Reliance Electric Motor, 3 hp, 1755 rpm, 230/460 V, 7.6/3.8 amps, 60 Hz, 3 phase. Sterling Electric Speed-Trol Variable Speed Drive, 4270 rpm (max), 460 rpm (min). Output pump and motor: G&H Centrifugal Pump, Model: GHH-10, S/N: 96-5-52830, impeller diameter: 5-1/2 in., (1) 2-1/2 in. Q-line suction inlet, (1) 2 in. dia. Q-line discharge outlet. Watlow Process Temperature Setpoint Indicator, Series: 965. Partlow MRC700 Temperature Recorder. Koss Industrial Control Panel with touchpad controls and digital display. Hammond Manufacturing Switch Box.





