

Baltimore Aircoil Company Fluid Cooler – 210 Tons

Mfg: Baltimore Aircoil Company

Model: VXI-210-2R

Stock No.: 280.264

Serial No.: 84-2973P

Baltimore Aircoil Company Fluid Cooler. Model VXI-210-2R S/N 84-2973P. Rated capacity: 210 nominal tons with respective entering and leaving water temperature of 95°F and 85°F and a wet bulb of 78°F. (2) U.S. fan motors: S/N(s): F-6317-06-941 / F-6317-06-974, 30 hp, 1750 rpm, 60 Hz, 79.6/39.8 Amps, 230/460V. (2) Paco pumps: S/N(s):FXMAO888460062014 / FXMA0888860062014. (2) General Electric pump motors: 5hp, 3510 rpm, 3 phase, 60 Hz, 230/460V. Features include: dual circuits, fan discharge dampers with 120V controls, electric water controls package with level control, (2) electric pan heaters: model: S713U221200U, 480V, 60Hz, 3 phase. Inlets: (2) 4 in. Outlets: (2) 4 in. Drain: 4 in. Approximate shipping and operating weights: 30130lbs.and 44620lbs. Overall dimensions: 18 ft. 1 in. L x 6 ft. 2 in. W x 4 ft. 10 in. H.(ACN870-84).



