

Aquionics Inc. UV System

Mfg: Aquionics

Model: UV125A

Stock No.: 40.BP5a

Serial No.: 2389

Aquionics Inc. UV System. Model: UV125A. S/N: 2389. Power supply: 220 V, 60 Hz, 2500 watts. (2) Hanovia UV Monitors, S/N: 465. (2) Hanovia Transformers, type: 1KW, Primary V: 220/240, Secondary V: 380/420, KVA Nom: 1.26, 60 Hz, single phase. (2) Biprol Impregnated Capacitors, max rated current: 50 amps, 500 Vrms. Hanovia Keystone Pneumatic Actuator. Inlets: (2) 1-1/2 in. dia. S-line fittings. Outlet: (1) 2 in. dia. flanged port. Overall dimensions: 3 ft. L x 2 ft. 4 in. W x 5 ft. 5 in. H.









