

Stainless Steel Slicer

Mfg:

Model:

Stock No. 3R-2018A.1

Serial No.

Stainless Steel Slicer. Maximum aperture/clearance above belt: 1-1/2 in. W x 1/2 in. H. Height at conveyor inlet/outlet: 45-1/2 in. Infeed belt dimensions: 48 in. L x 1-1/2 in. W. Aligning belt dimensions: 17 in. L x 1 in. W. Cutting wheel diameter: 5-1/4 in. Product is guided downwards, through the discharge, by a 4-pronged placing wheel. Excess liquids accumulate in a 20 in. L x 4-1/2 in. W dish. Reliance Electric Motor, 3/4 hp, 1725 rpm, 230/460 V, 4.6/2.3 amps, 60 Hz, 3 phase. Reeves Motor Drive, 6.1 ratio, 764 rpm (max), 76.4 rpm (min). Inlets: 1/2 in. dia. threaded fitting. Outlets: 2 in. L x 2 in. W discharge chute. Overall dimensions: 55 in. L x 29 in. W x 56 in. H. Hub City Drive, 2 ratio. Ohio Drive, 8 ratio.





