Krones Pre-Mix System	
Mfg: Krones	Model: 8402
Stock No: 950.BP7a	Serial No:

Krones Pre-Mix System. Model: 8402. 316 stainless steel. (2) 100 gallon vertical mix tanks skid-mounted, S/N's: M534 063 D & M526 066 P. Operating pressure: 8 bar. Operating temperature: 20° C. LTC 1220 level transmitter. Bran & Lubbe Dosierpumpe Proportioning System, Type: N-C32, S/N: 51-78763. Antriebstechnik Motor, 460/230 V, 10/20 amps. (2) Hilge Centrifugal Pumps, Type: HYGIA BL. I/25A, Nr's: 86 74 196 and 86 74 197. (2) Hilge Motors, 3500 rpm, 460 V, 2.85 amps, 60 Hz, 1.5 kW. Inlets/outltets: (1) 1/2 in. dia. pipe, (1) 3/4 in. dia. pipe, (1) 1 in. dia. male ferrule, (1) 1 in. dia. threaded fitting, (1) 1 in. dia. FPT, (1) 1-1/2 in. dia. Q-line fitting, (2) 1-1/2 in. dia. threaded fittings. Overall dimensions: 6 ft. 10 in. L x 6 ft. W x 9 ft. 8 in. H. Krones designed the system to inject syrup into water in uniform quantities and carbonate if desired. Was used for essence in bottle water and to flavor bottle water. Rate of proportion: 100 GPM.

































































