

Tri-Clover Tri-Blender

Mfg: Tri Clover

Model:

Stock No.: ATGP007

Serial No.:

Tri-Clover Tri-Blender. Infeed hopper dimensions: 1 ft. 11 in. dia. x 1 ft. 6 in. H. Capacity for dry ingredients: up to 100 lbs. / min. depending on product. Liquid flow rate: up to 110 gpm depending on product. Materials of construction include: 316L/304 stainless steel. Maximum product temp: 140°F. Impeller diameter: 8 in. Baldor washdown-duty motor, 10 hp, 3500 rpm, 230/460 V, 23/11.5 amps, 60 Hz, 3 phase. Tri-Blenders are designed to blend dry ingredients with liquids, minimizing the introduction of air into the process. Applications include the food, beverage, dairy and biopharmaceutical industries. Inlets: (1) 1-1/2 in. dia. S-line fitting (infeed), (1) 2 in. dia. S-line fitting (infeed). Outlets: (1) 2 in. dia. S-line fitting. Overall dimensions: 2 ft. 10 in. L x 1 ft. 8 in. W x 4 ft. H.(ACN324).







BALDOR
WASHDOWN DUTY MOTOR
 BALDOR ELECTRIC CO.
 FT. SMITH AR. MFG. IN U.S.A.

CAT. NO.	540187111		
SPEC.	3745761223-1		
HP	10		
VOLTS	230/460		
AMPS	23/11.5		
R.P.M.	3500		
FRAME	2057G	HZ	60 PH 3
SER. F	1.03	CODE	DES. P. CLASS
NEMA NOM. EFF.	88.5	% P.F.	97.5
RATING	500 AMP-DEPT		
CC	1900	USABLE AT 208V	
BEARINGS	DE	1000	
ENCL.	TEFC	SN	