

Tri Clover Centrifugal Pump

Mfg: Tri Clover

Model: C216MF56T-S

Stock No. BFLV151.3a

Serial No. S12182

Tri Clover Centrifugal Pump. Model: C216MF56T-S. S/N: S12182. Pump capacity: 45 gpm at 30 ft. Impeller: 5 in. diameter. Leeson Motor, 1 hp, 1725 rpm, 208-230/460 V, 3.6-3.8/1.9 amps, 60 Hz, 3 phase. C-Series centrifugal pumps are engineered to deliver dependable performance and easy maintenance in virtually any low-viscosity application. Sample applications include: pharmaceutical, biotechnology, fine chemical, food, beverage and dairy processing industries. Inlet: 3-1/2 in. 'S' line. Outlet: 1-1/2 in. 'S' line. Overall dimensions: 18 in. L x 10 in. W x 10 in. H.

