

## Parker 25 HP Steam Boiler

Mfg: Parker Boiler Co.

Model: 103-25

Stock No. BIIR201.

Serial No.

### Parker Boiler Co. 25 hp Steam Boiler.

- 1997 Parker 25 HP Steam Boiler,
- Model 103-25.
- Max Rating BTU p/hr: 1,075,000.
- 25 hp steam boiler.
- Minimum Input rating BTU p/hr. 537.500.
- Sales Order 960001,
- Type of fuel: Natural gas. Max gas manifold pressure 4, required fuel inlet supply pressure 7-14 in. W.C. 480 volt.
- Minimum clearance to combustible construction:
- Cabinet, Sides and Rear: 12 in.
- Cabinet top: 48 in.
- Draft hood vent connector 6 in.
- Barometric damper chimney connector: 12 in.
- Wiring Diagram No. 100 GC2 3T5R2.
- Electrical Service boiler and pump. 460 volt, 60 hz, 3 phase.
- National board number 47937.
- Maximum allowable working pressure when built: 150 psi.
- Heating surface 132 sq. ft.
- Maximum designed steaming cap. 863 lb/hr.
- Parker boiler freewater system,
- Model R4-15003.
- Tank ORR1336,
- Pump: Burks pump. Catalog no. 37CT7M, SN 934163. Electrical 460/60/3.
- Franklin Electric Motor. Model 1303242103, 60 hz, 208-230/460 volt, 3/4 hp, 3,450 rpm, FLA 3.0/1.5. SFA 3.8/1.9, 9622CT, 60 hz, 50 frame.
- Overall dimensions: 59 in. W, 68 in. L, 57 in. H.





LISTED GAS FIRED BOILER ASSEMBLY NO. AN-156337 PARKER BOILER CO.	
<b>PARKER BOILER CO.</b> 5930 BANDINI BLVD.-LOS ANGELES, CA 90040 - (213) 727-9800	
103-25 MODEL NUMBER	1,075,000 MAXIMUM INPUT RATING, BTU/HR
25 HP STEAM BOILER DESCRIPTION	537,500 MINIMUM INPUT RATING, BTU/HR
960001 SALES ORDER NUMBER	NATURAL GAS TYPE OF FUEL
150 SAFETY VALVE & TRIM MAX. PRESSURE, PSI CAUTION: DO NOT INCREASE PRESSURE OF SAFETY VALVE WITHOUT CONSULTING THE INSPECTION AUTHORITY FOR APPROVAL	4 MAX. GAS MANIFOLD PRESSURE, IN. W.C. 7-14"W.C. REQUIRED FUEL INLET SUPPLY PRESSURE



