

## Sullair Ammonia Screw Compressor - 250 HP

Mfg: Sullair

Model: C25LB717-3.7

Stock No.: BNCA166.10

Serial No.: 056-R02088

Sullair Ammonia Screw Compressor Package. Model: C25LB717-3.7-250HP. S/N: 056-R02088. Capacity: 456 tons using R-717 at a 10°F suction temperature and a 95°F condensing temperature. Reliance electric motor: ID no. P44GO353C-G3-XM/MN2443, 250 hp, 3550 rpm, 460 V, 280 amps, 60 Hz, 3 phase. Oil separator, Nat'l Bd: 3018, S/N: 1-9231, Part No. 12817, Nat'l Board: 3018, Sullair control panel. Displacement: 1,710 cfm. Vi Setting: 3.7. Vessel: 300 psi @ 250°F, Shell thickness: 0.4375 in., head thickness: 0.375 in., inside straight wall dimensions: 32 in. dia. x 88 in. L. Max press ratings: 150 psig. Connections: 8 in. suction and 5 in. discharge. Inlets: (1) 10 in. dia. flanged port, (1) 2-1/2 in. dia. port. Outlets: (1) 6 in. dia. flanged port, (1) 2-1/2 in. dia flanged port. Approximate weight: 11,000 lbs. Overall dimensions: 14 ft. L x 5 ft. W x 9 ft. H.(ACN503a-BC/Motor-87).







