

## Fristam FKL-150 Positive Displacement Pump - 15 HP

Mfg: Fristam

Model: FKL150

Stock No.: CAGC904

Serial No.: 007708

Fristam rotary lobe positive displacement pump. Model FKL-150. Serial 007708. Max pressure: 300 PSI. Displacement per revolution: 0.259 gallons. Max flowrate: 155.4 gallons per minute at 600 RPM. GE motor: 15 HP, 208-230/460V, 1760 RPM, 254TCY frame, 60 Hz, 3-phase, TE. Gear reduction drive. Stainless steel base. Ports: 3 in. clamp. (ACN115)

