

Fristam FKL-150 Positive Displacement Pump - 7.5 HP

Mfg: Fristam

Model: FKL150

Stock No.: CAGC920

Serial No.: 007706

Fristam rotary lobe positive displacement pump. Model FKL-150. Serial 007706. Max pressure: 300 PSI. Displacement per revolution: 0.259 gallons. Max flowrate: 155.4 gallons per minute at 600 RPM. GE motor: 7.5 HP, 1755 RPM, 213TCY frame, 60 Hz, 3-phase, TE. Nord gear reduction drive: 11.71 ratio. Final RPM: 150 (38.85 GPM). Stainless steel base. Ports: 3 in. clamp. (ACN115)



